



GLANCE® POWERIZED PROFESSIONAL GLASS & SURFACE CLEANER

Version Number: 3

Preparation date: 2017-01-25

1. IDENTIFICATION

Product name: GLANCE® POWERIZED PROFESSIONAL GLASS & SURFACE CLEANER
Product Code: CBD539636, CBD539629, CBD540298, CBD540304, CBD540311, CBD540465
SDS #: MS0801108
Recommended use:

- Glass Cleaner
- This product is intended to be used neat.

Uses advised against: Uses other than those identified are not recommended

Manufacturer, importer, supplier: US Headquarters Diversey, Inc. 2415 Cascade Pointe Blvd. Charlotte, NC 28208 Phone: 1-888-352-2249 SDS Internet Address: https://sds.sealedair.com	Canadian Headquarters Sealed Air - Canada 3755 Laird Road Mississauga, Ontario L5L 0B3 Phone: 1-800-668-7171
---	--

Emergency telephone number: 1-800-851-7145; 1-651-917-6133 (Int'l)

2. HAZARDS IDENTIFICATION

Classification for the undiluted product

This product is not classified as hazardous according to OSHA 29CFR 1910.1200 (HazCom 2012-GHS) and Canadian Hazardous Products Regulations (HPR) (WHMIS 2015-GHS).

Precautionary Statements

None required.

Health hazards not otherwise classified (HHNOC) - Not applicable

Physical hazards not otherwise classified (PHNOC) - Not applicable

Classification for the diluted product @ RTU

This product is intended to be used neat.

Precautionary Statements

See undiluted product information above.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Classified Ingredients

None of the components of this product are classified as hazardous according to OSHA 29CFR 1910.1200 (HazCom 2012-GHS) and Canadian Hazardous Products Regulations (HPR) (WHMIS 2015-GHS).

4. FIRST AID MEASURES

Undiluted Product:

Eyes: Rinse with plenty of water. If irritation occurs and persists, get medical attention.

Skin: Rinse with plenty of water. If irritation occurs and persists, get medical attention.

Inhalation: No specific first aid measures are required.

Ingestion: Rinse mouth with water.

Most Important Symptoms/Effects: No information available.

Immediate medical attention and special treatment needed: Not applicable.

Aggravated Medical Conditions: None known.

Diluted Product:

This product is intended to be used neat.

Eyes: See undiluted product information above.

Skin: See undiluted product information above.

Inhalation: See undiluted product information above.

Ingestion: See undiluted product information above.

5. FIRE-FIGHTING MEASURES

Specific methods: No special methods required

Suitable extinguishing media: The product is not flammable. Extinguish fire using agent suitable for surrounding fire.

Specific hazards: Not applicable.

Special protective equipment for firefighters: As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Extinguishing media which must not be used for safety reasons: No information available.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions: No special measures required.

Environmental precautions and clean-up methods: Clean-up methods - large spillage. Absorb spill with inert material (e.g. dry sand or earth), then place in a chemical waste container. Use a water rinse for final clean-up.

7. HANDLING AND STORAGE

Handling: Handle in accordance with good industrial hygiene and safety practice. FOR COMMERCIAL AND INDUSTRIAL USE ONLY.

Storage: Protect from freezing. Keep tightly closed in a dry, cool and well-ventilated place. KEEP OUT OF REACH OF CHILDREN.

Aerosol Level (if applicable): Not applicable

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Exposure Guidelines:

Undiluted Product:

Engineering measures to reduce exposure:

No special ventilation requirements. General room ventilation is adequate.

Personal Protective Equipment

Eye protection: No special requirements under normal use conditions.

Hand protection: No special requirements under normal use conditions.

Skin and body protection: No special requirements under normal use conditions.

Respiratory protection: No special requirements under normal use conditions.

Hygiene measures: Handle in accordance with good industrial hygiene and safety practice.

Diluted Product:

This product is intended to be used neat.

Personal Protective Equipment

Eye protection:	No personal protective equipment required under normal use conditions.
Hand protection:	No personal protective equipment required under normal use conditions.
Skin and body protection:	No personal protective equipment required under normal use conditions.
Respiratory protection:	No personal protective equipment required under normal use conditions.
Hygiene measures:	Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State: Liquid	Color: Clear, Light, Blue
Evaporation Rate: No information available	Odor: Ammonia
Odor threshold: No information available.	Boiling point/range: Not determined
Melting point/range: Not determined	Decomposition temperature: Not determined
Autoignition temperature: No information available	Solubility: Completely Soluble
Solubility in other solvents: No information available	Relative Density (relative to water): No information available
Density: No information available. lbs/gal Kg/L	Vapor density: No information available
Bulk density: No information available	Vapor pressure: No information available.
Flash point (°F): > 200 °F > 93.3 °C	Partition coefficient (n-octanol/water): No information available
Dilution Flash Point: @RTU	Viscosity: No information available
Elemental Phosphorus: - % by wt.	VOC: 0.33 % *
pH: 10.5	VOC % by wt. at use dilution % *
Dilution pH: No information available. @ RTU	Flammability (Solid or Gas): Not applicable
Corrosion to metals: Not corrosive	Sustained combustion: Not applicable
Explosion limits: - upper: Not determined - lower: Not determined	

* - Title 17, California Code of Regulations, Division 3, Chapter 1, Subchapter 8.5, Article 2, Consumer Products, Sections 94508

10. STABILITY AND REACTIVITY

Reactivity:	Not Applicable
Stability:	The product is stable
Hazardous decomposition products:	None reasonably foreseeable.
Materials to avoid:	Do not mix with any other product or chemical unless specified in the use directions.
Conditions to avoid:	No information available.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure:

Eye contact, Skin contact, Inhalation, Ingestion

Delayed, immediate, or chronic effects and symptoms from short and long-term exposure

Skin contact: Unlikely to be irritant in normal use.

Eye contact: May be mildly irritating to eyes.

Ingestion: No information available.

Inhalation: No information available.

Sensitization: No known effects.

Target Organs (SE): None known

Target Organs (RE): None known

Numerical measures of toxicity mg/kg

12. ECOLOGICAL INFORMATION

Ecotoxicity: No information available.

Persistence and Degradability: No information available.

Bioaccumulation: No information available.

13. DISPOSAL CONSIDERATIONS

Waste from residues / unused products (undiluted product): This product, as sold, if discarded or disposed, is not a hazardous waste according to Federal regulations (40 CFR 261.4 (b)(4)). Dispose in compliance with all Federal, state, provincial, and local laws and regulations.
Waste from residues / unused products (diluted product): Not applicable.

RCRA Hazard Class (undiluted product): Not Regulated
RCRA Hazard Class (diluted product): Not Applicable
Contaminated Packaging: Do not re-use empty containers.

14. TRANSPORT INFORMATION

DOT/TDG/IMDG: Proper shipping descriptions can vary by pack size. Please refer to the Diversey HazMat Library, <http://naextranet.diversey.com/dot/>, for up to date shipping information.

DOT (Ground) Bill of Lading Description: NON REGULATED ITEM CLEANING, WASHING, BUFFING, OR POLISHING COMPOUNDS LIQUID

IMDG (Ocean) Bill of Lading Description: NON REGULATED ITEM CLEANING, WASHING, BUFFING, OR POLISHING COMPOUNDS LIQUID

15. REGULATORY INFORMATION

International Inventories at CAS# Level

All components of this product are listed on the following inventories: U.S.A. (TSCA), Canada (DSL/NDSL).

This product is not subject to the reporting requirements under California's Proposition 65.

RIGHT TO KNOW (RTK)

Ingredient(s)	CAS #	MARTK:	NJRTK:	PARTK:	RIRTK:
Water	7732-18-5	-	-	-	-
Diethylene glycol butyl ether	112-34-5	-	X	-	-
2-butoxyethanol	111-76-2	X	X	X	-
Sodium lauryl sulfate	151-21-3	-	-	-	-
Ammonium hydroxide	1336-21-6	X	X	X	X

CERCLA/ SARA

Ingredient(s)	CAS #	Weight %	CERCLA/SARA RQ (lbs)	Section 302 TPQ (lbs)	Section 313
Diethylene glycol butyl ether	112-34-5	> 0.1 - < 1%			X
2-butoxyethanol	111-76-2	> 0.1 - < 1%			X
Ammonium hydroxide	1336-21-6	< 0.1%	1000		X

Ingredient(s)	CAA HAP	CAA ODS	CWA Priority Pollutants
Diethylene glycol butyl ether	X		
2-butoxyethanol	X		

SARA 311/312 Hazard Categories

Immediate: -
Delayed: -
Fire: -
Reactivity: -
Sudden Release of Pressure: -

Canadian Regulations

Ingredient(s)	CAS #	NPRI
Diethylene glycol butyl ether	112-34-5	X
2-butoxyethanol	111-76-2	X

16. OTHER INFORMATION

NFPA (National Fire Protection Association)
 Rating Scale: (Low Hazard) 0 - 4 (Extreme Hazard)

Health 0
Flammability 0

Instability 0

Version Number: 3
Preparation date: 2017-01-25

Reason for revision: Not applicable
Prepared by: NAPRAC
Additional advice: • Does not contain an added fragrance

Notice to Reader: This document has been prepared using data from sources considered technically reliable. It does not constitute a warranty, express or implied, as to the accuracy of the information contained within. Actual conditions of use and handling are beyond seller's control. User is responsible to evaluate all available information when using product for any particular use and to comply with all Federal, State, Provincial and Local laws and regulations.