



2550000374 - FOLGERS 22.6 OZ CLASSIC DECAF CAN

The original aromas and flavors of Folgers Coffee are still Americas favorites. This Mountain Grown coffee has been a part of Americas mornings for more than 150 years. When you serve Folgers your patrons enjoy Americas number 1 retail coffee brand. Makes up to 180 6 FO Cups; Mountain Grown; For All Coffee Makers; 99.7% Caffeine Free; Kosher

Brand: Folgers®



Nutrition Facts

Serving Size 8 FL OZ (240mlt)
Servings Per Container 0

Amount Per Serving

Calories 0

% Daily Value*

Total Fat 0 g 0%

Saturated Fat 0 g 0%

Trans Fat 0 g

Cholesterol 0 mg 0%

Sodium 0 mg 0%

Potassium 0 mg 0%

Total Carbohydrate 0 g 0%

Dietary Fiber 0 g 0%

Sugars 0 g

Protein 0 g

Vitamin A 0% • Vitamin C 0%

Calcium 0% • Iron 0%

Vitamin D 0%

*Percent Daily Values are based on a 2,000 calorie diet. Your daily values may be higher or lower depending on your calorie needs.

	Calories:	2,000	2,500
Total Fat	Less than	65g	80g
Sat Fat	Less than	20g	25g
Cholesterol	Less than	300mg	300mg
Sodium	Less than	2,400mg	2,400mg
Total Carbohydrate		300g	375g
Dietary Fiber		25g	30g

Calories per gram:

Fat 9 • Carbohydrate 4 • Protein 4

Ingredients

Decaffeinated Coffee.

Product Specifications

GTIN	10025500003747	Case Net Weight	8.48 LB
Item UPC	2550000374	Case L,W,H	19.50 IN, 13.13 IN, 4.81 IN
Unit Size	6 / 22.6OZ	Cube	0.71 CF
Shelf Life	450 Days	Tie x High	7 x 8
Case Gross Weight	10.53 LB	Kosher Status	Yes

Preparation and Cooking

For best brewing results we recommend: For 1 serving (6 FO) use 1 tablespoon of Folgers coffee. For 10 servings use 1/2 measuring cup of Folgers coffee.

Serving Suggestions

Rich pure taste. We specially roast and grind each Mountain Grown bean delivering pot after pot of rich flavors and aromas. Pure coffee satisfaction.

Packaging and Storage

Refrigerate after opening to help preserve flavor and aroma.