

Storage Precautions: Keep in cool, dry conditions in original containers at no more than 30° C

SECTION 8: EXPOSURE CONTROL AND PERSONAL PROTECTION

Occupational Exposure limit: Not Established

Protection: Although unexpected, avoid prolonged skin contact. Use chemically resistant gloves as needed.

Respiratory Protection: None required under normal usage

Eye Protection: None required

SECTION 9: PHYSICAL AND CHEMICAL PROPERTIES

Appearance: Cylindrical bottle with scented powder

Flash pt: Not applicable.

Relative Density: Not determined

Odor: Various

Evaporation Rate: Not applicable.

Solubility in water: Insoluble.

Odor Threshold: Not determined

Flammability: Not determined/applicable

Partition Coefficient: Not determined

Color: Light Brown

UEL: Not determined

Autignition Temperature: Not applicable

pH value: Not determined/applicable

LEL: Not determined

Decomposition Temperature:

Melting Pt: Estimated 60° C

Vapor Pressure: Not determined/applicable

Not determined/applicable

Boiling Pt: Not applicable.

Vapor Density: Not determined/applicable

SECTION 10: STABILITY AND REACTIVITY

Stability: Normally stable.

Conditions to avoid: Avoid extreme heat and naked flames.

Materials to avoid: Strong oxidizing agents.

Decomposition Products: None under normal storage conditions.

SECTION 11: TOXICOLOGICAL INFORMATION

Acute Effects: Ingredients include a small quantity of volatile fragrance chemicals which

Chronic Effects: None are known.

may contain small amounts of substances that are harmful if swallowed and/or irritating to the eyes and skin.

Health Risks: INHALATION: Prolonged exposure to volatile ingredients is unlikely to cause irritation or other adverse health effects.

INGESTION: No practical risk of adverse health effects.

SKIN CONTACT: No practical risk of adverse health effects.

EYE CONTACT: No practical risk of adverse health effects.

SECTION 12: ECOLOGICAL INFORMATION

No specific information has been established regarding the product. However according to the conventional method of Directive 99/45/EC the product is classified as harmful to aquatic organisms, or causing long-term effects in the aquatic environment.

Ecotoxicity: N/A

Bioaccumulative Potential: N/A

Persistence and Degradability: N/A

Mobility in Soil: N/A

Other Adverse Effects: N/A

SECTION 13: DISPOSAL CONSIDERATIONS

Dispose of in accordance with Local Authority requirements e.g., for used product, as household waste

SECTION 14: TRANSPORT INFORMATION

Product is not regulated as hazardous

Transport Hazard Class: N/A

DOT Classifications: Non Hazardous

UN-Number: N/A

Packing group: N/A

UN Proper Shipping Name: N/A

Marine Pollutant: N/A

Special Precautions with Transport: N/A

SECTION 15: REGULATORY INFORMATION

Classification, Packaging and Labeling according to Directive 99/45/EC

Signal word:

Pictograms:

WARNING

Exclamation mark

Hazard Phrases:

Precautionary Phrases:

P301+310: If swallowed, call physician

H302: Harmful if swallowed.

P102: Keep out of reach of children.

P302+P352: If on skin, wash with plenty of water.

H317: May cause allergic skin reaction.

P264: Wash hands thoroughly after handling.

P332+P313: If rash occurs, seek medical attention.

P280: Wear suitable gloves.

P501: Dispose of contents to an approved waste disposal plant.

SECTION 16: OTHER INFORMATION

This Safety Data Sheet was prepared to comply with the current OSHA Hazard Communication Standard (HCS) adoption of the Globally Harmonized System of Classification and Labeling of Chemicals (GHS)