

GUARDIAN MATS PRODUCT SPECIFICATIONS

FLEX STEP

Product Specifications

Construction Material	SBR Rubber
Available Colors	Black
Surface Pattern	Matte Dome
Overall Thickness	0.5825in
Anti-Static	Static Dissipative
Tensile Strength	1000lb/in ² min
Durometer	45
Weight Tolerance	± 5%
Size Tolerance	± 1%
Other	DOP Free
Mat Weight	LBS
2'x3'	7.435
3'x5'	21.84
Mat Dimensions	FEET
	2'x3'
	3'x5'

