

GUARDIAN MATS PRODUCT SPECIFICATIONS

SOFT STEP / AIR STEP

Product Specifications

Construction Material	Vinyl
Available Colors	Black, Grey, Black w/Yellow Border
Surface Pattern	Pebble, Ribbed
Overall Thickness	3/8 0.375in ± 10%, 5/8 0.625 ± 10%
Anti-Static	No
Tensile Strength	100lb/in ² min
Elongation	100% min
Durometer	65 ± 5
Tear	15lb/in min
Flammability	DOT FMVSS302, CPSC FF 1-70
Suggested Temperature	-20°F to +200°F
Mat Weight	LBS
2'x3'	5
3'x5'	10
Mat Dimensions	FEET
	2'x3'
	3'x5'