

GUARDIAN MATS PRODUCT SPECIFICATIONS

DUAL RIB

Product specifications

Benefits

Fiber Type	Polypropylene	Fade resistant
Dye Process	Solution Dyed	Color Fast
Face Weight (oz/yd ²)	18 ± 1	Plush Exterior
Rubber Polymer Type	Vinyl	Chemical Resistant
Extruded Base Sheet Thickness	54 mil	Helps Reduce Movement/ Durability
Antistatic	No	
Backing type	Smooth	Helps Reduce Movement
Edge Thickness	54 Mil ± 4 Mil	Durability / Safety
Border Width	1.000" ± 0.125"	Durability / Safety
Mat Weight	LBS	
2'x3'	3.0	
3'x5'	7.5	Helps Reduce Movement
4'x6'	12.0	Helps Reduce Movement
4'x8'	16.0	
3'x10'	15.0	Helps Reduce Movement
Weight Tolerance	± 5%	
Mat Dimensions	FEET	
	2'x3'	
	3'x5'	
	4'x6'	
	4'x8'	
	3'x10'	
Mat Length and Width Tolerance	± 1%	

