

1. IDENTIFICATION

Product Name	Tide Professional® Floor and All-Purpose Cleaner - Powder Concentrate
Product Code(s)	4-70
Product ID:	15154287_PROF_NG
Product Type:	Finished Product - Professional Use Only
Recommended Use	Floor Care
Restrictions on Use	Use only as directed on label.
Manufacturer	Procter & Gamble Professional 2 P&G Plaza Cincinnati, Ohio 45202 Procter & Gamble Inc. P.O. Box 355, Station A Toronto, ON M5W 1C5 1-800-332-7787
E-mail Address	pgsds.im@pg.com
Emergency Telephone	Transportation (24 HR) CHEMTREC - 1-800-424-9300 (U.S./ Canada) or 1-703-527-3887 Mexico toll free in country: 800-681-9531

2. HAZARD IDENTIFICATION

This product is classified under 29CFR 1910.1200(d) and the Canadian Hazardous Products Regulation as follows:.

Hazard Category	
Eye Damage / Irritation	Category 2B
Signal Word	WARNING
Hazard Statements	Causes eye irritation
Hazard pictograms	None
Precautionary Statements - Prevention	Wash hands thoroughly after handling
Precautionary Statements - Response	IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing If eye irritation persists: Get medical advice/attention IF SWALLOWED: Drink 1 or 2 glasses of water

Precautionary Statements - Storage None

Precautionary Statements - Disposal None

Hazards not otherwise classified (HNOC) None

3. COMPOSITION/INFORMATION ON INGREDIENTS

Ingredients are listed according to 29CFR 1910.1200 Appendix D and the Canadian Hazardous Products Regulation

Chemical Name	Synonyms	Trade Secret	CAS-No	Weight %
Sodium carbonate	-	No	497-19-8	30 - 35
Benzenesulfonic acid, mono-C10-16-alkyl derivs., sodium salts	-	No	68081-81-2	25 - 30
Silicic acid, sodium salt	-	No	1344-09-8	1 - 5

4. FIRST AID MEASURES

First aid measures for different exposure routes

Eye contact Rinse with plenty of water. Get medical attention immediately if irritation persists.

Skin contact Rinse with plenty of water. Get medical attention if irritation develops and persists.

Ingestion Drink 1 or 2 glasses of water. Do NOT induce vomiting. Get medical attention immediately if symptoms occur.

Inhalation Move to fresh air. If symptoms persist, call a physician.

Most important symptoms/effects, acute and delayed None under normal use conditions.

Indication of immediate medical attention and special treatment needed, if necessary

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable extinguishing media Dry chemical, CO₂, alcohol-resistant foam or water spray.

Unsuitable Extinguishing Media None.

Special hazard None known.

Special protective equipment for fire-fighters As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

Specific hazards arising from the chemical None.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal precautions Use personal protective equipment. Do not get in eyes, on skin, or on clothing.

Advice for emergency responders Use personal protective equipment as required.

Methods and materials for containment and cleaning up

Methods for containment Prevent dust cloud. Prevent further leakage or spillage if safe to do so.

Methods for cleaning up Sweep up and shovel into suitable containers for disposal. Dispose of in accordance with local regulations.

7. HANDLING AND STORAGE

Precautions for safe handling

Advice on safe handling Use personal protective equipment as required. Keep container closed when not in use. Never return spills in original containers for re-use. Keep out of the reach of children.

Conditions for safe storage, including any incompatibilities

Storage Conditions Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible products None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

Exposure Guidelines No exposure limits noted for ingredient(s).

Exposure controls

Engineering Measures **Distribution, Workplace and Household Settings:**
Ensure adequate ventilation

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Where reasonably practicable this should be achieved by the use of local exhaust ventilation and good general extraction

Personal Protective Equipment

Eye Protection **Distribution, Workplace and Household Settings:**
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Use appropriate eye protection

Hand Protection **Distribution, Workplace and Household Settings:**
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Protective gloves

Skin and Body Protection **Distribution, Workplace and Household Settings:**

No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
Wear suitable protective clothing

Respiratory Protection

Distribution, Workplace and Household Settings:
No special protective equipment required

Product Manufacturing Plant (needed at Product-Producing Plant ONLY):
In case of insufficient ventilation wear suitable respiratory equipment

9. PHYSICAL AND CHEMICAL PROPERTIES

Physical State @20°C solid
Appearance white
Odor mild
Odor threshold No information available

<u>Property</u>	<u>Values</u>	<u>Note</u>
pH value	9.5 - 11.3	(as 1% solution)
Melting/freezing point	No information available	
Boiling point/boiling range	No information available	
Flash point	No information available	
Evaporation rate	No information available	
Flammability (solid, gas)	No information available	
Flammability Limits in Air		
Upper flammability limit	No information available	
Lower Flammability Limit	No information available	
Vapor pressure	No information available	
Vapor density	No information available	
Relative density	0.36	
Water solubility	100%	
Solubility in other solvents	No information available	
Partition coefficient: n-octanol/water	No information available	
Autoignition temperature	No information available	.
Decomposition temperature	No information available	.
Viscosity of Product	No information available	

VOC Content (%) Products comply with US state and federal regulations for VOC content in consumer products.

10. STABILITY AND REACTIVITY

Reactivity None under normal use conditions.
Stability Stable under normal conditions.
Hazardous polymerization Hazardous polymerization does not occur.
Hazardous Reactions None under normal processing.
Conditions to Avoid None under normal processing.
Materials to avoid None in particular.
Hazardous Decomposition Products None under normal use.

11. TOXICOLOGICAL INFORMATION

Product Information

Information on likely routes of exposure

Inhalation	No known effect.
Skin contact	No known effect.
Ingestion	No known effect.
Eye contact	Irritating to eyes.

Delayed and immediate effects as well as chronic effects from short and long-term exposure

Acute toxicity	No known effect.
Skin corrosion/irritation	No known effect.
Serious eye damage/eye irritation	Irritating to eyes.
Skin sensitization	No known effect.
Respiratory sensitization	No known effect.
Germ cell mutagenicity	No known effect.
Neurological Effects	No known effect.
Reproductive toxicity	No known effect.
Developmental toxicity	No known effect.
Teratogenicity	No known effect.
STOT - single exposure	No known effect.
STOT - repeated exposure	No known effect.
Target Organ Effects	No known effect.
Aspiration hazard	No known effect.
Carcinogenicity	No known effect.

Component Information

Chemical Name	CAS-No	LD50 Oral	LD50 Dermal	LC50 Inhalation
Sodium carbonate	497-19-8	2800 mg/kg bw (Guideline not indicated; rat)	> 2000 mg/kg bw (EPA 16 CFR 1500.40; rabbit)	-
Benzenesulfonic acid, mono-C10-16-alkyl derivs., sodium salts	68081-81-2	1090.00 mg/kg (rat)	-	-
Silicic acid, sodium salt	1344-09-8	3400 mg/kg bw (Similar to OECD 401; standard acute method; rat)	> 5000 mg/kg bw (Read across data on AgSil TM 25 Potassium silicate solution; rat)	> 2.06 mg/L air (Read across data AgSil TM 25 Potassium silicate solution; EPA OPPTS 870.1300; standard acute method; rat)

12. ECOLOGICAL INFORMATION

Ecotoxicity

The product is not expected to be hazardous to the environment.

Persistence and degradability	No information available.
Bioaccumulative potential	No information available.
Mobility	No information available.
Other adverse effects	No information available.

13. DISPOSAL CONSIDERATIONS

Waste treatment

Waste from Residues / Unused Products	Disposal should be in accordance with applicable regional, national and local laws and regulations.
Contaminated packaging	Disposal should be in accordance with applicable regional, national and local laws and regulations.

California Hazardous Waste Codes 331
(non-household setting)

14. TRANSPORT INFORMATION

DOT Not regulated

IMDG Not regulated

IATA Not regulated

15. REGULATORY INFORMATION

U.S. Federal Regulations

SARA 313

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material

Clean Air Act, Section 112 Hazardous Air Pollutants (HAPs) (see 40 CFR 61)

This product does not contain any substances regulated as hazardous air pollutants (HAPS) under Section 112 of the Clean Air Act Amendments of 1990.

Clean Water Act

This product does not contain any substances regulated as pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42)

California Proposition 65

This product is not subject to warning labeling under California Proposition 65.

U.S. State Regulations (RTK)

Chemical Name	CAS-No	Massachusetts
Sulfuric acid sodium salt (1:2)	7757-82-6	X

Chemical Name	CAS-No	Pennsylvania
Sulfuric acid sodium salt (1:2)	7757-82-6	X

International Inventories

United States

All intentionally-added components of this product(s) are listed on the US TSCA Inventory.

Canada

This product is in compliance with CEPA for import by P&G.

Legend

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

CEPA - Canadian Environmental Protection Act

16. OTHER INFORMATION

HMIS Ratings

Health hazard	-
Flammability	2
Physical hazard	0

NFPA Ratings

Health hazard	2
Flammability	0
Instability	0

Issuing Date: 09-Jan-2015

Revision Date: 07-Apr-2015

Disclaimer

The information provided in this Safety Data Sheet is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guidance for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process, unless specified in the text

End of SDS