



## Quartet® InvisaMount™ Magnetic Glass Marker Board, 50" x 28", White Surface, Frameless

Premium glass board features InvisaMount™ for even more contemporary, sleek aesthetics.

G5028IMW

### Product Description

Dress up any work area with a premium glass board. Classic whiteboard functionality is enhanced with the up-to-the-minute aesthetic appeal of glass and an invisible mounting system. The board appears to float on the wall to provide an unobstructed sheet of glass for all your creative needs.

### Features

- Tempered glass surface whiteboard is stain and ghost resistant to ensure clean erasability and top notch durability
- Glass is magnetic and offers a smooth writing surface. Use with dry-erase makers and rare earth magnets to write messages and post papers.
- Frameless design fits in seamlessly with modern office space décor, and allows boards to be lined up side-by-side for an extended writing platform
- 50" x 28" board size is wide format to match 16:9 aspect ratio projection screens and televisions
- Writing in all colors is easily visible on the white glass board surface and glass is easy to keep clean with Quartet® whiteboard cleaning supplies
- InvisaMount™ feature with hidden hardware maximizes usable board space and gives the whiteboard a floating appearance on the wall. Template is included to aid in mounting accuracy.
- Included aluminum marker tray is detachable. Clips on easily to store accessories or can be removed for a sleeker look.
- Magnetic glass whiteboard comes with 1 Quartet dry-erase marker and 2 round magnets
- Limited 20 year warranty

### Specifications

- **Detailed Color** White
- **Mounting Hardware Type** Invisible Mount
- **Orientation** Horizontal
- **Period of Warranty** 20 years
- **Standard Board Size** 50" x 28"
- **Usage** Public Space - High traffic
- **Use Frequency** Heavy Use
- **Whiteboard Printed Surface** None

### Other information

- **Dimensions** 50" x 28"



### Case information

Depth	2.63"
Width	55.13"
Height	43.44"
Gross weight	40.80lbs
UPC#	034138223314
Unit quantity	1

### Shipping Information

Country of origin	CN
Minimum Order Quantity	1
Lowest possible unit	Each

### General information

Color	Unknown
Layer/Pallet	18
Cases/Layer	1

[www.quartet.com](http://www.quartet.com)

