

# 019-12001 through 019-12009

## Ladder Climb System, Complete Kit

#### **FEATURES:**

- · 2-person top bracket with energy-absorbing head unit
- 3/8" corrosion-resistant galvanized steel cable
- · Pre-swaged termination for added protection
- 3,600 lb. single user anchor point
- · Tension retaining base bracket adjusts to conditions
- · All mounting hardware included
- · Product inspection label included
- · Cable sleeve and intermediate guides sold separately
- System capacity: up to 620 lbs. (281.2 kg) when used with the EVO or any ANSI Z359.16 rated detachable cable sleeves

### FALL ARREST POINT(S):

· D-ring on top bracket

#### **ITEM WEIGHT:**

· See chart below

USER WEIGHT CAPACITY		
ANSI	130-310 lbs. (59-141 kg)	
OSHA	Up to 420 lbs. (191 kg)	

SIZE(S)			
019-12001	20 ft. (6.1 m) / 21.8 lbs. (9.9 kg)		
019-12002	30 ft. (9.1 m) / 23.8 lbs. (10.8 kg)		
019-12003	40 ft. (12.2 m) / 25.8 lbs. (11.7 kg)		
019-12004	50 ft. (15.2 m) / 27.8 lbs. (12.6 kg)		
019-12005	60 ft. (18.3 m) / 29.8 lbs. (13.5 kg)		
019-12006	70 ft. (21.3 m) / 31.8 lbs. (14.4 kg)		
019-12007	80 ft. (24.4 m) / 33.8 lbs. (15.3 kg)		
019-12008	90 ft. (27.4 m) / 35.8 lbs. (16.2 kg)		
019-12009	100 ft. (30.5 m) / 37.8 lbs. (17.1 kg)		



STANDARD COMPLIANT WITH			
ANSI	A14.3		
OSHA	1926.1053, 1910.29, 1926.502, 1910.140		

COMPONENT	MATERIAL SPECIFICATION
Top Bracket	Galvanized Steel, Powder coated stain- less steel
Bottom Bracket	Galvanized steel, stainless steel
Cable	3/8" Galvanized steel cable
U-Bolts/Nuts	Zinc plated steel
D-ring	Powder coated carbon steel
Label	Stainless steel