



019-12012 through 019-12021 Cable Assembly

FEATURES :

- 3/8" corrosion-resistant galvanized steel cable
- Steel thimble to protect cable eye
- Pre-swaged termination for added protection
- Custom lengths also available by request

FALL ARREST POINT(S) :

- N/A

ITEM WEIGHT :

- See chart below



| USER WEIGHT CAPACITY | |
|----------------------|-----|
| ANSI | N/A |
| OSHA | N/A |

| STANDARD COMPLIANT WITH | |
|-------------------------|-----|
| ANSI | N/A |
| OSHA | N/A |

| SIZE(S) | |
|-----------|-------------------------------------|
| 019-12012 | 20 ft. (6.1 m) / 4 lbs. (1.8 kg) |
| 019-12013 | 30 ft. (9.1 m) / 6 lbs. (2.7 kg) |
| 019-12014 | 40 ft. (12.2 m) / 8 lbs. (3.6 kg) |
| 019-12015 | 50 ft. (15.2 m) / 10 lbs. (4.5 kg) |
| 019-12016 | 60 ft. (18.3 m) / 12 lbs. (5.4 kg) |
| 019-12017 | 70 ft. (21.3 m) / 14 lbs. (6.3 kg) |
| 019-12018 | 80 ft. (24.4 m) / 16 lbs. (7.2 kg) |
| 019-12019 | 90 ft. (27.4 m) / 18 lbs. (8.2 kg) |
| 019-12020 | 100 ft. (30.5 m) / 20 lbs. (9.1 kg) |
| 019-12021 | Custom Length |

| COMPONENT | MATERIAL SPECIFICATION |
|-----------|-----------------------------|
| Cable | 3/8" Galvanized steel cable |
| Thimble | Galvanized steel |
| Ferrules | Aluminum |
| | |
| | |
| | |