



019-4007

Girder Grip Anchor

FEATURES :

- Quick installation and removal from rated metal or steel structures
- Use horizontally or vertically
- Fits hole diameter minimum 13/16" min. up to 1-1/4"
- Installs into steel substrate with a maximum thickness of 1-1/4"
- Dimensions: 1/4" x 2" x 4-1/2"
- Minimum Breaking Strength: 5,000 lbs.

FALL ARREST POINT(S) :

- 1 O-ring

ITEM WEIGHT :

- .6 lbs. (.3 kg)



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-140.6 kg)
OSHA	Up to 420 lbs. (190.5 kg)

STANDARD COMPLIANT WITH	
ANSI	a
OSHA	1926.502

SIZE(S)	
N/A	

COMPONENT	MATERIAL SPECIFICATION
Anchor	Zinc Plated Steel