



020-1212 through 020-1218

PRO+ Slate Full Body Harness : Alu 1D, Alu QC Chest, Alu FD, TB Legs

FEATURES :

- Dorsal D-ring
- Dorsal SRL link
- Front D-ring
- Quick-connect chest
- Quick torso adjusters
- Tongue buckle legs
- Shoulder pad
- Removable leg pads

FALL ARREST POINT(S) :

- 1 Dorsal D-ring
- 1 Dorsal SRL link

ITEM WEIGHT :

- 4.4 lbs. (2.1 kg)



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-140.6 kg)
OSHA	Up to 420 lbs. (190.5 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.11-2021
OSHA	1926.502, 1910.140

SIZE(S)	
020-1212	X-Small
020-1213	Small
020-1214	Medium
020-1215	Large
020-1216	X-Large
020-1217	2X
020-1218	3X

COMPONENT	MATERIAL SPECIFICATION
Webbing	Polyester
D-ring(s)	Anodized aluminum
Adjuster buckles	Anodized aluminum
Chest connection	Anodized aluminum
Leg connection	Steel tongue buckle w/ SS grommets
Dorsal SRL link	Polyester
Pads	Nubuck synthetic; Spandex; Poly mesh; EVA