



020-1266 through 020-1272

Arc Flash Full Body Harness : DE 3D, DE QC Chest, DE FD, TB Legs

FEATURES :

- Dorsal D-ring
- Front D-ring
- Side positioning D-rings
- Quick-connect chest
- Mating buckle torso adjusters
- Tongue buckle legs
- Component backers
- Shoulder pad
- Fixed leg pads
- 40 Cal rated aramid webbing

FALL ARREST POINT(S) :

- 1 Dorsal D-ring

ITEM WEIGHT :

- 4.8 lbs. (2.2 kg)



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-140.6 kg)
OSHA	Up to 420 lbs. (190.5 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.11-2021
OSHA	1926.502, 1910.140
ASTM	F887

SIZE(S)	
020-1266	X-Small
020-1267	Small
020-1268	Medium
020-1269	Large
020-1270	X-Large
020-1271	2X
020-1272	3X

COMPONENT	MATERIAL SPECIFICATION
Webbing	Aramid
D-ring(s)	Dielectric alloy steel
Adjuster buckles	Dielectric alloy steel
Chest connection	Dielectric alloy steel
Leg connection	Steel tongue buckle w/ SS grommets
Component backers	NB synthetic; FR treated poly; NBR rubber
Pads	Nomex ®