



021-1617 through 021-1621

V-Line Construction Harness : 3D, QC Chest, TB Legs

FEATURES :

- Dorsal D-ring
- Side positioning D-rings
- Quick-connect chest
- Friction buckle torso adjusters
- Tongue buckle legs
- Shoulder pad
- Floating waist pad

FALL ARREST POINT(S) :

- 1 Dorsal D-ring

ITEM WEIGHT :

- 5.5 lbs. (2.5 kg)



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-140.6 kg)
OSHA	Up to 420 lbs. (190.5 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.11-2021
OSHA	1926.502, 1910.140

SIZE(S)	
021-1617	Small
021-1618	Medium
021-1619	Large
021-1620	X-Large
021-1621	2X

COMPONENT	MATERIAL SPECIFICATION
Webbing	Polyester
D-ring(s)	Zinc plated alloy steel
Adjuster buckles	Zinc plated alloy steel
Chest connection	Zinc plated alloy steel
Leg connection	Steel tongue buckle w/ SS grommets
Pads	Polyester mesh; EVA
Belt	Polyester; Steel; Stainless steel