021-1810-1815

Reflective Full Body Harness: 1D, MB Chest, TB legs, Mining belt

FEATURES:

- 1 Dorsal D-Ring
- Fixed mating buckle chest
- · Friction torso adjusters
- · Pull-down adjustment
- · Tongue buckle legs
- · Tool strap on each hip
- · Removable shoulder pad
- · Radio loop on each shoulder
- · Tool ring on each shoulder
- 2 Replacement lanyard keepers
- Adjustable mining belt for lamp and battery
- · Hi-vis reflective webbing

FALL ARREST POINT(S):

· 1 Dorsal D-ring

ITEM WEIGHT:

• 4.6 lbs. (2.1 kg)

ABOVE: Front and Back of Harness
RIGHT: Front of Harness in the dark with flash
photography to show reflective web quality

USER WEIGHT CAPACITY		
ANSI	130-310 lbs (59-140.6 kg)	
OSHA	up to 420 lbs (190.5 kg)	

SIZE(S)		
021-1810	Small	
021-1811	Medium	
021-1812	Large	
021-1813	X-Large	
021-1814	2X	
021-1815	3X	

STANDARD COMPLIANT WITH		
ANSI	Z359.11-2021, 107-2021	
OSHA	1926.502, 1910.140	

COMPONENT	MATERIAL SPECIFICATION
Webbing	Hi-vis polyester
D-ring	Zinc plated alloy steel
Adjuster buckles	Zinc plated alloy steel
Chest connection	Zinc plated alloy steel
Leg connection	Steel tongue buckle w/ SS grommets
Pad	Polyester mesh; EVA
Tool Rings	Steel
Lanyard Keepers	Velcro; Nylon plastic
Belt	PVC w nylon fiber; Steel buckle