



021-4043

10K Swivel Anchor & Back Plate

FEATURES :

- Designed for reinforced cinder block, chillers, or AC unit walls
- Use with 10k Swivel Anchor
- Maximum span up to 12"
- Coated Steel Plate 6" x 4" x 1/4"
- 5/8" Bolt and wingnut included
- Minimum breaking strength 10,000lbs

FALL ARREST POINT(S) :

- Swivel Anchor

ITEM WEIGHT :

- 4.95lbs (2.25kg)



USER WEIGHT CAPACITY	
ANSI	310lbs (140.6kg)
OSHA	420lbs (190.5kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.18-2017 Type A
OSHA	1926.502, 1910.66

SIZE(S)	
N/A	

COMPONENT	MATERIAL SPECIFICATION
10K Swivel Anchor	Zinc plated steel
Back Plate	Zinc plated steel
5/8" Bolt	Steel
Wingnut	Zinc plated steel