



021-4062

5K Swivel Steel Anchor

FEATURES :

- 180° / 360° rotating connection point
- Installs quickly for temporary or permanent anchor point
- Used vertically or horizontally
- Minimum breaking strength : 5,000lbs
- Fastener not included

FALL ARREST POINT(S) :

- 1 D-ring

ITEM WEIGHT :

- 1.2lbs (.5kg)



USER WEIGHT CAPACITY	
ANSI	130-310lbs (140.6kg)
OSHA	420lbs (190.5kg)

STANDARD COMPLIANT WITH	
ANSI	A10.32, Z359.18-2017 Type A
OSHA	1926.502, 1910.66

Replacement Part # (s)	
N/A	

COMPONENT	MATERIAL SPECIFICATION
Anchor	Zinc plated steel