



021-4068

Beam Walker Easy Slider 3.5"-14"

FEATURES :

- 180° rotating connection point
- Lightweight aluminum construction
- Easy trailing for hands-free work
- One-handed trigger with dual sided adjustment
- Nylon rollers for more effective slide
- Replaceable nylon jaw liners to extend product life span
- Fits beams 3-1/2" to 14" with flanges up to 1-1/4"
- For overhead and foot level tie-off
- Protective label cover
- Overall length 19-1/2"
- Minimum breaking strength : 5,000 lbs.

FALL ARREST POINT(S) :

- 1 D-ring

ITEM WEIGHT :

- 3.6 lbs. (1.6 kg)



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (141 kg)
OSHA	Up to 420 lbs. (191 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.18-2017 (Type A)
OSHA	1926.502, 1910.140

RELATED PRODUCTS	
021-4071	Replacement 2 Jaws w/4 Fasteners (for 021-4068)

COMPONENT	MATERIAL SPECIFICATION
Support bar	Aluminum
Clamps	Aluminum
D-ring	Plated Steel
Jaws	Nylon
Rollers	Nylon
Label Cover	Polyester



021-4069

Beam Walker Easy Slider 12”-30”

FEATURES :

- 180° rotating connection point
- Lightweight aluminum construction
- Easy trailing for hands-free work
- One-handed trigger with dual sided adjustment
- Nylon rollers for more effective slide
- Replaceable nylon jaw liners to extend product life span
- Fits beams 12” to 30” with flanges up to 2-5/8”
- For overhead and foot level tie-off
- Protective label cover
- Overall length 37”
- Minimum breaking strength : 5,000 lbs.

FALL ARREST POINT(S) :

- 1 D-ring

ITEM WEIGHT :

- 5.2 lbs. (2.4 kg)



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (141 kg)
OSHA	Up to 420 lbs. (191 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.18-2017 (Type A)
OSHA	1926.502, 1910.140

RELATED PRODUCTS	
021-4072	Replacement 2 Jaws w/4 Fasteners (for 021-4069)

COMPONENT	MATERIAL SPECIFICATION
Support Bar	Aluminum
Clamps	Aluminum
D-ring	Plated Steel
Jaws	Nylon
Rollers	Nylon
Label Cover	Polyester