



021-4082

5K Swivel D-ring Anchor

FEATURES :

- 180°/360° rotation
- Installs quickly as a temporary or permanent anchor point
- Requires pre-drilled hole of 5/8" to a minimum depth of 5-3/8"
- Used vertically or horizontally
- Installs with the 5/8" expansion bolt (not included)
- Zinc-plated stamped steel D-ring anchor
- Zinc-plated base, bushing and washer
- Length : 6"
- Width : 3"
- Minimum Breaking Strength : 5,000lbs

FALL ARREST POINT(S) :

- 1 D-ring

ITEM WEIGHT :

- 0.68 lbs. (0.31 kg)



USER WEIGHT CAPACITY	
ANSI	130-310lbs (140.6kg)
OSHA	420lbs (190.5kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.18-2017 Type A
OSHA	1926.502, 1910.66

Replacement Part # (s)	
021-4083	5K Swivel D-ring Anchor Bushing/Washer Set

COMPONENT	MATERIAL SPECIFICATION
D-ring Anchor	Zinc plated alloy stamped steel
Base	Zinc plated alloy steel
Bushing	Zinc plated alloy steel
Washer	Zinc plated alloy steel