



022-2087

Arc Flash 6' Energy Absorbing Lanyard : Aramid, Dielectric Snap Hook, Soft Loop

FEATURES :

- 40Cal/750F rated
- 1 Soft loop
- 1 Dielectric snap hook
- Hook tensile strength: 5,000 lbs. (2268 kg)
- Hook gate rating: 3,600 lbs. (1633 kg)
- Single leg construction

ATTACHMENT POINT(S) :

- 1 Soft loop
- 1 Dielectric snap hook

ITEM LENGTH :

- 6' (1.8 m)

ITEM WEIGHT :

- 2.3 lbs. (1 kg)



USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-140.6 kg)
OSHA	N/A

STANDARD COMPLIANT WITH	
ANSI	Z359.13-2013
OSHA	1926.502, 1910.66
ASTM	F887

SIZE(S)	
N/A	

COMPONENT	MATERIAL SPECIFICATION
Webbing	1 3/4" Aramid
Wear sleeve	Aramid
Shock pack	Nomex®
Snap hook	Dielectric
Soft loop	Aramid
Thread	Kevlar®