



## 023-1235 through 023-1240

### PRO Full Body Harness : 1D, MB Chest, TB Legs, Trauma Relief

#### FEATURES :

- Dorsal D-ring
- Mating buckle chest
- Friction buckle torso adjusters
- Tongue buckle legs
- Shoulder pad
- Integrated Quick-Adjust Trauma Relief packs (022-6047) installed on the harness for temporary relief while awaiting rescue.

#### FALL ARREST POINT(S) :

- 1 Dorsal D-ring

#### ITEM WEIGHT :

- 4.6 lbs. (2.1 kg)



**BUILT-IN TRAUMA RELIEF PACKS**

USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-140.6 kg)
OSHA	Up to 420 lbs. (190.5 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.11-2021
OSHA	1926.502, 1910.140

SIZE(S)	
023-1235	X-Small
023-1236	Small / Medium
023-1237	Large / X-Large
023-1238	2X
023-1239	3X
023-1240	4X

COMPONENT	MATERIAL SPECIFICATION
Webbing	Polyester
D-ring	Zinc plated alloy steel
Adjuster buckles	Zinc plated alloy steel
Chest connection	Zinc plated alloy steel
Leg connection	Steel tongue buckle w/ SS grommets
Pad	Polyester mesh; EVA
Trauma Relief	Polyester, EP coated stainless steel, Velcro