



023-1241 through 023-1248

PRO+ Construction Harness: 3D, QC Chest, TB Legs, Trauma Relief

FEATURES :

- Dorsal D-ring
- Dorsal SRL link
- Side positioning D-rings
- Quick-connect chest
- Quick torso adjusters
- Tongue buckle legs
- Shoulder pad
- Floating comfort waist pad
- Removable leg pads
- Integrated Quick-Adjust Trauma Relief packs (022-6047) installed on the harness for temporary relief while awaiting rescue.

FALL ARREST POINT(S) :

- 1 Dorsal D-ring
- 1 Dorsal SRL link

ITEM WEIGHT :

- 6.3 lbs. (2.8 kg)



BUILT-IN TRAUMA RELIEF PACKS

USER WEIGHT CAPACITY	
ANSI	130-310 lbs. (59-140.6 kg)
OSHA	Up to 420 lbs. (190.5 kg)

STANDARD COMPLIANT WITH	
ANSI	Z359.11-2021
OSHA	1926.502, 1910.140

	SIZE(S)
023-1241	X-Small
023-1242	Small
023-1243	Medium
023-1244	Large
023-1245	X-Large
023-1246	2X
023-1247	3X
023-1248	4X

COMPONENT	MATERIAL SPECIFICATION
Webbing	Polyester
D-ring(s)	Zinc plated alloy steel
Adjuster buckles	Anodized aluminum
Chest connection	EP alloy steel
Leg connection	Steel tongue buckle w/ SS grommets
Dorsal SRL link	Polyester
Pads	Nubuck synthetic; Polyester mesh; EVA
Belt	Polyester; Steel; Stainless steel
Trauma Relief	Polyester, EP coated stainless steel, Velcro