



020-1352 thru 020-1358

Arc Flash Full Body Harness:
1D, MB Chest, TB Legs

**Features and Benefits**

Dorsal D-ring
Tongue buckle legs
Shoulder, and leg pads
Friction buckle torso adjusters
40Cal/700F rated aramid webbing

Mating buckle chest
Component backer

Fall Arrest Attachment Point(s)

Dorsal D-ring

Attachment Point(s)

N/A

Weight

2.5 lbs (1.1 kg)

User Weight Capacity

ANSI 130-310 lbs (140.6 kg)
OSHA Up to 420 lbs (190.5 kg)

Standards Compliant With

ANSI	Z359.11
OSHA	1926.502
ASTM	F887

Sizes

020-1352-XS	020-1355-L	020-1358-3X
020-1353-S	020-1356-XL	
020-1354-M	020-1357-2X	

Material Specifications:	
Webbing	40 Cal/700° Char rated Aramid
D-ring(s)	Plated Steel (Dorsal)
Torso Adjusters	Plated steel
Chest Connection	Plated steel mating buckle
Leg Connection	Zinc Plated Steel Buckles Stainless Steel Grommets
Padding	Nomex®
Component Backer	NBR Rubber