



019-8038, 019-8046, and 020-8060

SafeLink 42" I-Beam Stanchion

FEATURES :

- Durable zinc plated steel construction
- Single or Multi-Span up to 60' (18.3 m). Total system length is indefinite
- Built in carrying handle
- Easy bolt and wingnut installation
- Mounts to I-Beams in various lengths
- Fit I-beam flanges up to 2 1/4" thick
- Use with most HLL systems
- Maximum 2 users per span

FALL ARREST POINT(S) :

- N/A

ITEM WEIGHT :

- 36.5lbs (16.5kg)



USER WEIGHT CAPACITY	
ANSI	130-310lbs (140.6kg)
OSHA	N/A

STANDARD COMPLIANT WITH	
ANSI	N/A
OSHA	1926.502, 1910.66

SIZE(S)	
019-8038	4" to 18"
019-8046	4" to 24"
020-8060	4" to 12"

COMPONENT	MATERIAL SPECIFICATION
I-Beam Upright	YCM Plated Steel
I-Beam Base	YCM Plated Steel
I-Beam Clamp	Clear Zinc Plated Steel