

























QUA-016, rev.: 00



DENOMINACIÓN GENÉRICA / GENERIC NAME		MINICANAL / MINITRUNKING			
DIRECTIVA APLICADA / DIRECTIVE APLIED		2014/35/UE REBT 2002: Reglamento de Baja Tensión <i>REBT 2002: Low Tension Norm.</i>			
CLASIFICACIÓN / CLASSIFICATION		TIPO DE MATERIAL: AISLANTE <i>TYPE OF MATERIAL: ISOLATED</i>			
		MODO DE FIJACIÓN / FIXATION PLACE: • SUPERFICIE / WALL			
		LUGAR PREVISTO / ENVIROMENT: INTERIOR			
		GRADO DE PROTECCIÓN / PROTECTION DEGREE: IP20			
		RESISTENCIA AL IMPACTO / IMPACT RESISTANCE: IK07			
		TENSIÓN DE AISLAMIENTO / ISOLATED TENSION: 1000 V			
		TAPA DESMONTABLE / COVER REMOVABLE			
HILO INCANDESCENTE / GLOW WIRE		650 °C			
ESTABILIDAD DIMENSIONAL / DIMENSIONAL STABILITY		TEMPERATURA / TEMPERATURE: - 15 °C / + 70 °C HUMEDAD RELATIVA / HUMIDITY: 100 % HR			
CARACTERÍSTICAS CONSTRUCTIVAS / BUILD CHARACTERISTICS.		FIJACIÓN CON TORNILLO / FIXING WITH SREWS: - Blanco RAL 9016: 71518, 71528, 71529, 71538, 71547, 71557, 71560, 71567, 71577, 71587, 71544, 71564, 71596, - Efecto Madera: 71618, 71628, 71629			
		AUTOADHESIVO / SELF-ADHESIVE: - Blanco RAL 9016: 71518-A, 71528-A, 71529-A, 71538-A, 71557-A, 71560-A. - Efecto Madera: 71618-A, 71628-A, 71629-A			
DIMENSIONES / DIMENSIONS					
Ref. Item 71518		7x12 apertura tapa / 7x12 with cover	Ref. Item 71529		10x20 apertura tapa / 10x20 with cover
Ref. Item 71518-A		7x12 apertura tapa autoadhesivo / 7x12 self-adhesive with cover	Ref. Item 71529-A		10x20 apertura tapa autoadhesivo / 10x20 self-adhesive with cover
Ref. Item 71528		10x16 apertura tapa / 10x16 with cover	Ref. Item 71538		12x12 apertura tapa / 12x12 with cover
Ref. Item 71528-A		10x16 apertura tapa autoadhesivo / 10x16 self-adhesive with cover	Ref. Item 71538-A		12x12 apertura tapa autoadhesivo / 12x12 self-adhesive with cover
Ref. Item 71547		10x35 apertura tapa / 10x35 with cover	Ref. Item 71577		20x50 apertura tapa / 20x50 with cover
Ref. Item 71557		16x16 apertura tapa / 16x16 with cover	Ref. Item 71587		20x60 apertura tapa / 20x60 with cover
Ref. Item 71560		16x25 apertura tapa / 16x25 with cover	Ref. Item 71544		40x40 apertura tapa / 40x40 with cover
Ref. Item 71567		16x40 apertura tapa / 16x40 with cover	Ref. Item 71564		40x60 apertura tapa / 40x60 with cover
Ref. Item 71618		7x12 apertura tapa / 7x12 with cover	Ref. Item 71596		60x90 apertura tapa / 60x90 with cover
Ref. Item 71618-A		7x12 apertura tapa autoadhesivo / 7x12 self-adhesive with cover	Ref. Item 71628-A		10x16 apertura tapa autoadhesivo / 10x16 self-adhesive with cover
Ref. Item 71628		10x16 apertura tapa / 10x16 with cover	Ref. Item 71629		10x20 apertura tapa / 10x20 with cover
			Ref. Item 71629-A		10x20 apertura tapa autoadhesivo / 10x20 self-adhesive with cover
NORMA APLICADA / STANDARD APPLIED			EN 50085-1		



Realizado y aprobado por:
Made and approved by:



J. Ferrando