

KETCHAM TECHNICAL DATA

Deluxe Illuminated Series

LED Top Light



Model 173-TL-LED

Surface Mounted Data

| Stainless Steel Frame | Overall Size W x H x D | Door Size W x H | Cabinet Body Depth | Glass Shelves |
|-----------------------|---|-----------------|----------------------------------|---------------|
| 171-TL-LED | 16" x 23 ⁵ / ₈ " x 8" | 16" x 20" | 4 ⁵ / ₁₆ " | 2 |
| 173-TL-LED | 16" x 33 ⁵ / ₈ " x 8" | 16" x 30" | 4 ⁵ / ₁₆ " | 3 |

| Lumens | Watts | Kelvin |
|--------|-------|--------|
| 630 | 5.75 | 6000 |

Specifications: White baked enamel 20 gauge rust resistant steel. Cabinets are hinged on the left.

Mirrors/Doors: 3/16" first quality plate glass framed with bright annealed stainless steel. Doors are mounted on a full length piano hinge and are equipped with a magnetic door catch.

Shelves: 1/4" adjustable tempered glass shelves mounted on locking adjustable aluminum shelf clips.

Lighting: Features integral hardwired LED lighting included. LED chip count is 21.

3505 Veterans Memorial Hwy., Suite S1
Ronkonkoma NY 11779



631-615-6151
www.ketchamcabinets.com