










## TR50VA004

Transformer 50 VA, 480/277/240/120 to 24 Vac, Circuit Breaker, Foot and Dual Threaded Hub Mount















## **SPECIFICATIONS**

VA Rating: 50 Frequency: 50/60 Hz

Mounting: Foot & Dual Threaded Hubs

Over Current Protection: Circuit Breaker

Dimensions: 3.475" x 2.513" x 3.014" (w/ .500" NPT Hubs) Wire Length: 8"Typical w/ .5" Strip

Operating Temperature: -30 to 140° F

MTBF: 100,000 Hours @ 77° F

Construction: Split-Bobbin

Approvals: Class 2 UL5085-3 Listed, C-UL, CE, RoHS