

B9000 3-Channel Soldering Station with soldering iron and safety rest, 120V

- ESD-safe station, iron, and heat-resistant silicon cable for safe handling
- High power performance soldering station
- Three preset memory channels
- High precision soldering iron with tool-less tip change
- Intuitive heat control knob
- Ergonomic handle
- Secured iron storage for maximum protection
- Easy-to-read LCD display
- Auto shut-off and sleep modes
- Includes soldering station, soldering iron, safety rest, tip cleaner, cleaning sponge and power cord



Specifications

Power Supply:	120V/60Hz
Rate Power:	22W
Max. Power:	120W
Temperature Range:	212 to 896°F (100 to 480°C)
Accuracy:	±10%
Stability:	±35.6°F (2°C)
Temperature Correction Type:	Digital PID correction
Display:	LCD
Channels:	3
ESD Safe:	Yes
Product Certifications:	CE, RoHS, FCC, ETL, CSA
Operating Temperature:	32 to 104°F (0 to 40°C)
Storage Temperature:	-4 to 176°F (-20 to 80°C)
Operating Humidity Range:	35 to 45%
Storage Humidity Range:	35 to 45%
Dimensions:	5.43 x 4.4 x 3.54" (138 x 112 x 90mm)
Weight:	4.6lbs (2.1kg)

Model	Description
B9000	3-Channel Soldering Station