

### TECHNICAL DATA

#### Features

##### Model R1404 Buffer Solution

- 4.01 pH Buffer Solution (25°C)
- 16.9 fl oz (500ml) bottle with viewing strip and childproof cap
- Color-coded red for easy identification
- ±0.020pH accuracy
- Certificate of Analysis available upon request

##### Model R1407 Buffer Solution

- 7.00 pH Buffer Solution (25°C)
- 16.9 fl oz (500ml) bottle with viewing strip and childproof cap
- Color-coded green for easy identification
- ±0.020pH accuracy
- Certificate of Analysis available upon request

##### Model R1410 Buffer Solution

- 10.00 pH Buffer Solution (25°C)
- 16.9 fl oz (500ml) bottle with viewing strip and childproof cap
- Color-coded blue for easy identification
- ±0.020pH accuracy
- Certificate of Analysis available upon request

##### Model R1420 Electrode Storage Solution

- Manufactured specifically for pH and ORP electrodes
- Specially formulated to minimize microbial growth
- 16.9 fl oz (500ml) bottle with childproof cap

##### Model R1425 Electrode Cleaning Solution

- Manufactured specifically for pH and ORP electrodes
- 16.9 fl oz (500ml) bottle with childproof cap

##### Model R1430 Conductivity Standard Solution

- 1413µS Conductivity Value (@20°C)
- 16.9 fl oz (500ml) bottle with childproof cap
- ±20µS or 1.0% accuracy
- Certificate of Analysis available upon request



R1404



R1407



R1410



R1420



R1425



R1430

Continued...

#### R1400-KIT

pH Buffer Solution Kit, 4.01, 7.00 and 10.00 pH



Includes:  
R1404 4.01 pH buffer solution,  
R1407 7.00 pH buffer solution &  
R1410 10.00 pH buffer solution

#### R1400-KIT2

Electrode Care and Maintenance Kit



Includes:  
R1420 Electrode Storage Solution &  
R1425 Electrode Cleaning Solution

| Model      | Description                                   |
|------------|---|
| R1404      | Buffer Solution, 4.01 pH                      |
| R1407      | Buffer Solution, 7.00 pH                      |
| R1410      | Buffer Solution, 10.00 pH                     |
| R1420      | Electrode Storage Solution                    |
| R1425      | Electrode Cleaning Solution                   |
| R1430      | Conductivity Standard Solution, 1413 $\mu$ s  |
| R1400-KIT  | pH Buffer Solution Kit, 4.01, 7.00 & 10.00 pH |
| R1400-KIT2 | Electrode Care and Maintenance Kit            |