



## Features

### Model R2300 Infrared Thermometer

- Built-in laser pointer identifies target area
- User selectable °F or °C
- 12:1 distance to spot size ratio
- Digitally adjustable emissivity
- Max and Min readings
- Backlit display
- High and low alarms
- Low battery indication and auto shut off
- Includes battery

### Model R5500 Circuit Breaker Finder

- Simply plug the transmitter into a receptacle and scan breaker box to identify the circuit
- Detects 5 3-wire receptacle wiring faults
- Built-in GFCI receptacle check function
- Adjustable sensitivity wheel quickly identifies breaker
- Audible (buzzer) and visual (LED) indicators assist in identification
- Includes transmitter and battery

### Model R6018 Dual Moisture Meter

- Pin and Pinless functions detect moisture in wood and building materials
- Audible alert and Data Hold functions
- Built-in measurement verification and battery check
- Low battery indicator and auto shut-off
- Includes pins, protective cap and battery

### Model R5110 Non-Contact Voltage Detector with Flashlight

- Suitable for receptacles or against insulated wire
- Double insulated housing for increased safety
- Audible (buzzer) and visual (LED) indicators
- Built-in flashlight
- Pocket clip
- Auto shut off
- Cat. IV 1000V safety rating
- Includes batteries

*Continued...*

#### Model R8005 Laser Distance Meter

- Designed for one-handed operation
- User selectable unit of measure (imperial/metric)
- Laser target pointer
- Reference point selection (front or rear of instrument)
- Quick, self calculation with real-time readout
- Backlit multi-line LCD display
- Area, Volume and Max/Min functions
- Addition, Subtraction and indirect 2/3 point (Pythagoras) calculations
- Integrated bubble level (Horizontal and vertical)
- Continuous measurement mode
- Internal memory saves up to 99 readings
- Low battery indicator and auto shut off
- Includes batteries

#### Model R9300 Combustible Gas Leak Detector

- Detects a wide range of combustible gases including: gasoline, propane, natural gas and fuel oil
- High sensitivity detects small leaks
- Designed for one-handed operation
- 16" (406mm) gooseneck for hard to reach areas
- User adjustable sensitivity wheel
- Alarm set at 10% LEL for methane
- Earphone jack for loud environments (earphones sold separately)
- Tricolor visual indicator
- Audible (variable tick rate) and visual (LED) alarm indicators
- User replaceable sensor
- Includes batteries

#### Model R1910 Compact Temperature & Humidity Meter

- Measures ambient temperature and relative humidity
- Designed for one-handed operation
- Backlit dual LCD display
- User selectable °F/°C
- Max, min and data hold functions
- Low battery indicator and auto shut off
- Includes batteries

#### Model R9950 Large Soft Carrying Case

- Accommodates up to 3 small to medium sized instruments
- Built-in elastics and compartments help organize instruments
- Adjustable shoulder strap and hand strap
- Made of polyester
- Internal dimensions: 12 x 9.5 x 2" (305 x 241 x 51mm)
- External dimensions: 12.5 x 10 x 2.5" (318 x 254 x 64mm)
- Weight: 8.2oz (232g)

Model	Description
RINSPECT-KIT 2	Deluxe Home Inspection Kit