



Features

Model R2300 Infrared Thermometer

- Built-in laser pointer identifies target area
- User selectable °F or °C
- 12:1 distance to spot size ratio
- Digitally adjustable emissivity
- Max and Min readings
- Backlit display
- High and low alarms
- Low battery indication and auto shut off
- Includes battery

Model R5210 Receptacle Tester with GFCI

- Compact design
- Detects most common 3-wire receptacle issues
- LED indicators identify 5 wiring faults
- Status indicator chart
- GFCI trip test

Model R6018 Dual Moisture Meter

- Pin and Pinless functions detect moisture in wood and building materials
- Audible alert and Data Hold functions
- Built-in measurement verification and battery check
- Low battery indicator and auto shut-off
- Includes pins, protective cap and battery

Model R5110 Non-Contact Voltage Detector with Flashlight

- Suitable for receptacles or against insulated wire
- Double insulated housing for increased safety
- Audible (buzzer) and visual (LED) indicators
- Built-in flashlight
- Pocket clip
- Auto shut off
- Cat. IV 1000V safety rating
- Includes batteries

Model R1910 Compact Temperature & Humidity Meter

- Measures ambient temperature and relative humidity
- Designed for one-handed operation
- Backlit dual LCD display
- User selectable °F/°C
- Max, min and data hold functions
- Low battery indicator and auto shut off
- Includes batteries

Continued...

TECHNICAL DATA

Model R9300 Combustible Gas Leak Detector

- Detects a wide range of combustible gases including: gasoline, propane, natural gas and fuel oil
- High sensitivity detects small leaks
- Designed for one-handed operation
- 16" (406mm) gooseneck for hard to reach areas
- User adjustable sensitivity wheel
- Alarm set at 10% LEL for methane
- Earphone jack for loud environments (earphones sold separately)
- Tricolor visual indicator
- Audible (variable tick rate) and visual (LED) alarm indicators
- User replaceable sensor
- Includes batteries

Model R8005 Laser Distance Meter

- Designed for one-handed operation
- User selectable unit of measure (imperial/metric)
- Laser target pointer
- Reference point selection (front or rear of instrument)
- Quick, self calculation with real-time readout
- Backlit multi-line LCD display
- Area, Volume and Max/Min functions
- Addition, Subtraction and indirect 2/3 point (Pythagoras) calculations
- Integrated bubble level (Horizontal and vertical)
- Continuous measurement mode
- Internal memory saves up to 99 readings
- Low battery indicator and auto shut off
- Includes batteries

Model R2160 Thermal Imaging Camera

- 160 x 120 infrared resolution (19,200 pixels)
- 2.8" color TFT Display
- Built-in LED flashlight
- Choice of 5 color palettes
- High and Low temperature spot and alarm indicators
- Dustproof and 6.5' (2m) drop tested
- Rechargeable li-ion battery
- Tripod mountable for continuous long-term monitoring
- View stored data with included software
- Low battery indication and auto shut off
- Includes USB cable, lens cover, 16GB Micro SD Card

Model R8500 Recordable 8mm Video Inspection Camera

- Camera and video functions save high resolution images and video
- Comfortable pistol grip design
- High resolution 2.7" color LCD monitor
- 8mm waterproof (IP67) camera head
- Gooseneck cable retains configured shape
- Cable expandable up to 30 ft. (~9m) with extensions (optional)
- Six high visibility LED lights provide illumination in dimly lit environments
- Expandable memory up to 32Gb (SD card sold separately)
- Mirror rotation and Picture-in-Picture functions
- Low battery indicator and auto shut off
- Includes Video Borescope, 8mm Camera Head, Magnet, Hook, Mirror Attachments, Batteries, USB Cable

Model R9400 Carbon Monoxide Detector

- Backlit LCD displays CO levels from 0 to 1000ppm and ambient temperature
- User adjustable alarm limit (audible beep frequency increases as CO level rises)
- Quick response and high accuracy
- Data hold and max functions
- Self test sequence on start-up
- Low battery indicator and auto shut off
- Includes batteries

Model R9999 Industrial Tool Bag

- Rugged industrial tool bag with steel reinforced frame
- Ideal for hand tools, instruments and other small to medium sized items
- Large dual-zippered compartment with 11 internal pockets
- 12 outer mesh pockets for smaller tools
- Adjustable shoulder and hand straps
- Internal dimensions: 16 x 12 x 9" (406 x 305 x 229mm)
- External dimensions: 16.5 x 12.5 x 9.5" (420 x 318 x 241mm)
- Weight: 2.65lbs (1.2kg)

Model	Description
RINSPECT-KIT 3	Professional Home Inspection Kit