

# Product data sheet

## Characteristics

# HCM91TS

Trim, I-Line PNLBRD, hcm, surface, 4 pcs, 32x91x8.25 in



### Main

Range	I-Line
Product or Component Type	Trim
Parts Quantity	4

### Complementary

Width	32.25 in (819.15 mm)
Height	91 in (2311.40 mm)
Product Destination	Panelboard HCM 32 in (812.80 mm) 91 in (2311.40 mm) 8.25 in (209.55 mm)
Device Mounting	Surface
Net Weight	36.99 lb(US) (16.78 kg)

### Environment

Standards	CE CULus
-----------	-------------

### Ordering and shipping details

Category	00112 - I-LINE PB RTA TRIMS
Discount Schedule	PE1A
GTIN	00785901089186
Nbr. of units in pkg.	1
Package weight(Lbs)	37 lb(US) (16.78 kg)
Returnability	Yes
Country of origin	US

### Packing Units

Package 1 Height	0.12 ft (0.038 m)
Package 1 width	1.85 ft (0.564 m)
Package 1 Length	5.55 ft (1.692 m)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	Yes

---

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes

---

### Contractual warranty

---

Warranty	18 months
----------	-----------

---