



Main

Product or component type	Circuit breaker
Trip Unit Technology	Thermal-magnetic

Complementary

Line Rated Current	400 A
Number of Poles	3P
Breaking capacity code	H
Mounting Mode	Unit mount
Magnetic Hold Current	8000 A
Magnetic Tripping Current	9600 A
Electrical connection	Lugs load
Terminal identifier	AL400LA
Tightening torque	115.06 Lbf.in (13 N.m) 0.07...0.47 in ² (42...304 mm ²) (AWG 1...600 kcmil) 115.06 lbf.in (13 N.m) 0.07...0.20 in ² (42...127 mm ²) (AWG 1...250 kcmil)
Height	11 in (279.40 mm)
Width	6 in (152.40 mm)
Depth	5.84 in (148.34 mm)

Environment

Certifications	IEC CSA UL Listed
----------------	-------------------------

Ordering and shipping details

Category	00935 - LAL/LHL BRKR, SW, MAG-GARD
Discount Schedule	DE2
GTIN	00785901042273
Nbr. of units in pkg.	1
Package weight(Lbs)	16.24 lb(US) (7.37 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	11.90 in (30.226 cm)
Package 1 width	13.40 in (34.036 cm)
Package 1 Length	19.70 in (50.038 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

Contractual warranty

Warranty	18 months
----------	-----------