



Main

Product or component type	Dry Sealed Transformer
Primary to Secondary Voltage	277 V 120/240 V
Full Capacity Taps	0

Complementary

Enclosure Code	7A
Phase	1 phase
Power Rating	1 kVA
Temperature rise	115 °C
Height	8.13 in (206.50 mm)
Width	6.94 in (176.28 mm)
Depth	5.31 in (134.87 mm)
Enclosure mounting	Wall mounted
Enclosure material	Painted sheet steel

Environment

Enclosure Type	NEMA 3R
Insulation temperature	356 °F (180 °C)
Product certifications	UL Listed CULus CSA

Ordering and shipping details

Category	16277 - RESIN LVGP XFMR
Discount Schedule	PE2
GTIN	00785901014423
Nbr. of units in pkg.	1
Package weight(Lbs)	21.2 lb(US) (9.62 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	9.20 in (23.368 cm)
Package 1 width	10.20 in (25.908 cm)
Package 1 Length	11.20 in (28.448 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Phenyl glycidyl ether, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------