

### Main

Range	PowerLogic
Product or component type	I/O module
Device application	Optional expansion module
Range compatibility	PowerLogic PM8000 PowerLogic ION7400 PowerLogic ION9000

### Complementary

Number of outputs	2 form C relay output
Number of inputs	6 digital
Width	0.87 in (22 mm)
Depth	3.56 in (90.5 mm)
Height	3.56 in (90.5 mm)
Net Weight	4.94 oz (140 g)

### Environment

Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
IP degree of protection	IP30 IEC 60529



### Ordering and shipping details

Category	09782 - POWERLOGIC PM8000 ACCESSORIES
Discount Schedule	PL1
GTIN	00785901633402
Nbr. of units in pkg.	1
Package weight(Lbs)	0.49 lb(US) (0.22 kg)
Returnability	Yes
Country of origin	CN

### Packing Units

Package 1 Height	0.87 in (22.000 mm)
Package 1 width	3.56 in (90.500 mm)
Package 1 Length	3.56 in (90.500 mm)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 Yes

---

China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End Of Life Information</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

---