

Product data sheet

Characteristics

9050AO12EV06

Timing Relay, Type A, pneumatic, on delay, 0.1 to 60 seconds, 15A, 600 V, timed and instantaneous, 480 VAC 60 Hz coil



Main

| | |
|-------------------|---|
| Product range | 9050A/H |
| Product type | Timer |
| Timing Mode | On-delay |
| Timing Range | 0.1 s...1 min |
| Switch Function | SPDT |
| Coil Voltage | 480 V AC 60 Hz 440 V AC 50 Hz |
| Contact Operation | Time delayed 1 NO + 1 NC Instantaneous 2 NO + 2 NC |
| Current rating | 15 A |

Complementary

| | |
|---------------------------|---------------------------------------|
| Maximum switching voltage | 600 V AC |
| Electrical connection | Screw-clamp terminals |
| Reset response time | 29 Ms - on-delay 27 ms - off-delay |
| Mounting Support | Panel |

Environment

| | |
|---|--------------------------|
| Ambient Temperature Range - Operational | 68...104 °F (20...40 °C) |
| Certifications | CSA UL Listed |
| Height | 2.64 in (67 mm) |
| Width | 4.02 in (102 mm) |
| Depth | 4.37 in (111 mm) |

Ordering and shipping details

| | |
|-----------------------|---|
| Category | 21631 - 9050 A ONE MINUTE PNEUMATIC TIMER |
| Discount Schedule | CP1 |
| GTIN | 00785901493372 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 1.87 lb(US) (0.85 kg) |
| Returnability | No |
| Country of origin | MX |

Packing Units

| | |
|------------------|---------------------|
| Package 1 Height | 2.54 in (6.452 cm) |
| Package 1 width | 1.00 in (2.540 cm) |
| Package 1 Length | 6.45 in (16.387 cm) |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

| | |
|----------------------------|---|
| California proposition 65 | WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov |
| EU RoHS Directive | Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration |
| Mercury free | Yes |
| RoHS exemption information | Yes |
| China RoHS Regulation | China RoHS Declaration |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|