

RC2M200S

Meter mains, QO, combination service entrance, ringless socket, 200A, surface mount, no bypass



Main

Product or component type	Meter Mains
Range of product	QO

Complementary

Line Rated Current	200 A
Short-circuit current	22 kA
Network number of phases	1
Meter socket type	Ringless
Mounting	Surface
Number of spaces	0
Number of circuits	0
Number of Tandem Breakers	0
Hub type	A
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 6...300 kcmil aluminium/copper)line side AWG 8...AWG 2/0 2 aluminium/copper)service ground
Tightening torque	Lugs 250 lb.in, AWG 6...350 kcmil, aluminium/copper Lugs 250 lb.in, AWG 4...250 kcmil, aluminium/copper Service ground 50 lb.in, AWG 3...AWG 2/0, aluminium/copper Service ground 45 lb.in, AWG 6...AWG 4, aluminium/copper Service ground 40 lb.in, AWG 8, copper Lugs 50 lb.in, AWG 3...AWG 2/0, aluminium/copper Lugs 45 lb.in, AWG 6...AWG 4, aluminium/copper Lugs 40 lb.in, AWG 8, copper Cover 10 lb.in
Disconnect	Service disconnect (ordered separately)
Main Breaker Rating	200 A
Service feed location	OH UG
Bypass type	No bypass
Height	18.23 in (463.04 mm)
Width	19.58 in (497.33 mm)
Depth	4.60 in (116.84 mm)
Product certifications	UL E-6294

Environment

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Ordering and shipping details

Category	00022 - QO METER MAINS
Discount Schedule	DE3A
GTIN	00785901396697
Nbr. of units in pkg.	1
Package weight(Lbs)	27.5 lb(US) (12.47 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	5.50 in (13.970 cm)
Package 1 width	20.20 in (51.308 cm)
Package 1 Length	20.60 in (52.324 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------