



Main

| | |
|-----------------------------|-------------------------------------------------------------------------------------------------------------------------------|
| Range of product | Multi 9 |
| Product or component type | OC contact |
| Device short name | OFS |
| Signal contacts composition | 1 C/O |
| Line Rated Current | 3 A 380...415 V AC - 50/60 Hz 6 A 220...240 V AC - 50/60 Hz 1 A 130 V DC 1.5 A 60 V DC 2 A 48 V DC 6 A 24 V DC |
| 9 mm pitches | 1 |

Complementary

| | |
|-------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Range compatibility | Multi 9 C60 C60BP Multi 9 C60 C60BPR Multi 9 C60 C60SP Multi 9 GFP GFP Multi 9 C60H-DC C60H-DC |
| Mounting mode | Fixed |
| Mounting support | DIN rail |
| Height | 3.31 in (84 mm) |
| Width | 0.35 in (9 mm) |
| Depth | 2.87 in (73 mm) |
| Connections - terminals | Clamp terminal2 0.00 in ² (1.5 mm ²) - flexible Clamp terminal2 0.00 in ² (1.5 mm ²) - rigid Clamp terminal1 0.00...0.00 in ² (0.5...2.5 mm ²) - flexible Clamp terminal1 0.00...0.00 in ² (0.5...2.5 mm ²) - rigid |
| Wire stripping length | 0.35 in (9 mm) |
| Tightening torque | 8.85 lbf.in (1 N.m) |

Environment

| | |
|---------------------------------------|-------------------------------------------|
| Standards | EN/IEC 60947-5-1 |
| Product certifications | NEMKO DEMKO SEMKO CEBEC FIMKO |
| IP degree of protection | IP20 conforming to EN/IEC 60947-5-1 |
| Pollution degree | 3 conforming to EN/IEC 60947-5-1 |
| Tropicalisation | 2 conforming to EN/IEC 60947-5-1 |
| Relative humidity | 95 % 131 °F (55 °C) |
| Ambient air temperature for operation | -13...122 °F (-25...50 °C) |
| Ambient air temperature for storage | -40...185 °F (-40...85 °C) |

Ordering and shipping details




| | |
|-----------------------|-----------------------|
| Category | 01078 - DE2 MISC |
| Discount Schedule | DE2 |
| GTIN | 00785901930631 |
| Nbr. of units in pkg. | 1 |
| Package weight(Lbs) | 0.09 lb(US) (0.04 kg) |

| | |
|-------------------|----|
| Returnability | No |
| Country of origin | ES |

Packing Units

| | |
|------------------------------|-------------------------|
| Unit Type of Package 1 | PCE |
| Package 1 Height | 0.79 in (2 cm) |
| Package 1 width | 3.15 in (8 cm) |
| Package 1 Length | 3.74 in (9.5 cm) |
| Unit Type of Package 2 | BB1 |
| Number of Units in Package 2 | 12 |
| Package 2 Weight | 20.35 oz (577 g) |
| Package 2 Height | 3.54 in (9 cm) |
| Package 2 width | 3.94 in (10 cm) |
| Package 2 Length | 10.04 in (25.5 cm) |
| Unit Type of Package 3 | S03 |
| Number of Units in Package 3 | 108 |
| Package 3 Weight | 13.02 lb(US) (5.906 kg) |
| Package 3 Height | 11.81 in (30 cm) |
| Package 3 width | 11.81 in (30 cm) |
| Package 3 Length | 15.75 in (40 cm) |

Offer Sustainability

| | |
|----------------------------|---------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive | Compliant  EU RoHS Declaration |
| Toxic heavy metal free | Yes |
| Mercury free | Yes |
| RoHS exemption information |  Yes |
| China RoHS Regulation |  China RoHS Declaration |
| WEEE | The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins. |

Contractual warranty

| | |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|