

PDC6JD4

150 to 250A JD,JG,JJ,JL MOULDED CASE CIRCUIT BREAKER POWER DISTRIBUTION CONNECTO



Main

Range of product	Powerpact
Product or component type	Power distribution connector
Circuit breaker type	JJ JD JG JL
Quantity per set	Set of 3

Complementary

Line Rated Current	150...250 A
Tightening torque	35.40 Lbf.in (4.0 N.m) 0.02...0.04 in ² (10...25 mm ²) (AWG 8...AWG 4) 20.36 Lbf.in (2.3 N.m) 0.00...0.01 in ² (2.5...6 mm ²) (AWG 14...AWG 10)

Environment

Product certifications	CSA UL
------------------------	-----------

Ordering and shipping details

Category	01103 - H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES
Discount Schedule	DE2
GTIN	00785901598145
Nbr. of units in pkg.	1
Package weight(Lbs)	0.58 lb(US) (0.26 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	1.50 in (3.810 cm)
Package 1 width	3.50 in (8.890 cm)
Package 1 Length	4.90 in (12.446 cm)

Offer Sustainability

California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------
