



### Main

Range of product	Altivar
Accessory / separate part category	Mounting and fixing accessory
Accessory / separate part type	Mounting kit
Product compatibility	ATV61HC25N4D without braking unit ATV61HC25Y without braking unit ATV61HC31N4 without braking unit ATV61HC31N4D without braking unit ATV61HC31Y without braking unit ATV61HC40Y without braking unit ATV71HC20N4 without braking unit ATV71HC20N4D without braking unit ATV71HC20Y without braking unit ATV71HC25N4 without braking unit ATV71HC25N4D without braking unit ATV71HC25Y without braking unit ATV71HC28N4 without braking unit ATV71HC28N4D without braking unit ATV71HC31Y without braking unit ATV61HC25N4 Variable speed drive ATV600 250 kW, 380...480 V Variable speed drive ATV600 315 kW, 380...480 V Variable speed drive ATV900 250 kW, 380...480 V Variable speed drive ATV900 315 kW, 380...480 V
Accessory / separate part destination	Variable speed drive without braking unit
Range compatibility	Altivar 61 Altivar Process ATV600 Altivar 71 Altivar Process ATV900
Product specific application	For mounting the drive power section outside the enclosure

### Complementary

Kit composition	1 cutting and drilling template 1 fan support 1 user manual 1 metal frame of the right size for drive rating Corner pieces Fixing accessories seals
Net Weight	10.36 lb(US) (4.7 kg)

### Environment

Environmental characteristic	Dust and damp proof
------------------------------	---------------------

### Ordering and shipping details

Category	22135 - ATV61-71 ACCESSORIES
Discount Schedule	CP4C
GTIN	00785901481362
Nbr. of units in pkg.	1
Package weight(Lbs)	14.82 lb(US) (6.72 kg)
Returnability	No
Country of origin	CN

## Packing Units

Package 1 Height	1.000 dm
Package 1 width	3.000 dm
Package 1 Length	11.000 dm

## Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------