

Product data sheet

Characteristics

LJL36600U31X

Circuit breaker, PowerPact L, unit mount, Micrologic 3.3, 600A, 3 pole, 25 kA, 600 VAC, 80% rated



Main

Product or component type	Circuit breaker
---------------------------	-----------------

Complementary

Number of Poles	3P
Breaking capacity code	J
Electrical connection	Lugs load Lugs line
Terminal identifier	AL600LS52K3
Tightening torque	442.54 lbf.in (50 N.m) 0.11...0.37 in ² (70...240 mm ²) (AWG 2/0...500 kcmil)
Height	13.39 in (340.11 mm)
Width	7.27 in (184.66 mm)
Depth	6.61 in (167.89 mm)
Continuous current rating	80 %

Ordering and shipping details

Category	01116 - L ELEC TRIP UNIT MOUNT BREAKER/SW
Discount Schedule	DE2
GTIN	00785901891635
Nbr. of units in pkg.	1
Package weight(Lbs)	17.03 lb(US) (7.72 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	8.80 in (22.352 cm)
Package 1 width	14.00 in (35.560 cm)
Package 1 Length	31.70 in (80.518 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: DINP, which is known to the State of California to cause cancer, and DIDP, which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End Of Life Information
PVC free	Yes

Contractual warranty

Warranty	18 months
----------	-----------