



Main

Range	I-Line
-------	--------

Complementary

Main Type	Main lugs
Width	34.38 in (873.25 mm)
Height	48 in (1219.20 mm)
Product Destination	Panelboard interior HCP 42 in (1066.80 mm) 68 in (1727.20 mm)
Rated Current	600 A
Mounting Space	63 in (1600.20 mm)

Ordering and shipping details

Category	00016 - I-LINE PB RTA
Discount Schedule	PE1A
GTIN	00785901649847
Nbr. of units in pkg.	1
Package weight(Lbs)	160 lb(US) (72.57 kg)
Returnability	Yes
Country of origin	US

Packing Units

Package 1 Height	0.79 ft (0.241 m)
Package 1 width	3.17 ft (0.965 m)
Package 1 Length	4.25 ft (1.295 m)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Bisphenol A (BPA), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
RECh free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes

China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------
