

## Power Cord Adapter, NEMA 5-15R to NEMA L5-15P - Heavy-Duty, 15A, 120V, 14 AWG, 1 ft. (0.31 m), Black

MODEL NUMBER: P025-001



Heavy-duty extension cord converts a NEMA 5-15P plug into a locking NEMA L5-15P.

### Features

**Heavy-Duty Extension Cable for Network Devices That Require a Heavy-Gauge Connection** This 5-15R to L5-15R adapter features 14 AWG wire suitable for high power connections, making it a reliable solution for large server applications that require a higher-rated, heavier-gauge cable. It converts a standard NEMA 5-15P plug into a locking NEMA L5-15P plug, so it can connect to wall outlets, PDUs, surge protectors or UPS systems with NEMA L5-15R outlets. The 3-ft. (0.91 m) length helps reduce cable clutter and minimize the risk of tripping.

**Locking L5-15R Connector Helps Prevent Accidental Disconnection and Expensive Downtime** Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking NEMA L5-15R connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking cable is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the power cord always stays connected.

### Highlights

- Recommended for powering computers, servers and other network devices
- 1-ft. (0.31 m) length allows flexibility in placing devices, while avoiding cable clutter
- Heavy-duty power adapter replaces or upgrades standard cord provided by manufacturer
- Thick 14 AWG wire gauge manages high power levels required for larger equipment

### Applications

- Connect devices like computers, servers and monitors to a PDU in your data center
- Extend an existing power connection up to 1-ft. (0.31 m) to more easily place a device or reach a power source in a rack
- Update or replace the standard power cord provided by a device's original manufacturer

### Package Includes

- P025-001 5-15R to L5-15P Adapter Power Cord, 1-ft. (0.31 m), Black

## Specifications

OVERVIEW	
UPC Code	037332185891
Device Compatibility	Computer; Monitor/HDTV; Server; UPS; PDU
Country/Region	North America



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
www.tripplite.com

<b>INPUT</b>	
Maximum Input Amps	15
Voltage Compatibility (VAC)	120
<b>PHYSICAL</b>	
Color	Black
Number of Conductors	3
Wire Gauge (AWG)	14
Wire Gauge (OD - mm <sup>2</sup> )	2.08
Cable Length (ft.)	1
Cable Length (m)	0.3
Power Cord Jacket Type	SJT
Shipping Dimensions (hwd / cm)	22.40 x 32.69 x 1.27
Shipping Dimensions (hwd / in.)	8.82 x 12.87 x 0.50
Shipping Weight (kg)	0.18
Shipping Weight (lbs.)	0.40
<b>CONNECTIONS</b>	
Side A - Connector 1	NEMA L5-15P
Side B - Connector 1	NEMA 5-15R
<b>SPECIAL FEATURES</b>	
High Voltage	No
Locking Plug	Yes
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>