



## Main

Product or component type	Mechanically Held Lighting Contactor
Range of product	8903LX
Control Circuit	Separate control circuit

## Complementary

Control Voltage	110 V AC 50 Hz 120 V AC 60 Hz
Inrush power in VA	180 VA 60 Hz 150 VA 50 Hz 140 VA 50/60 Hz
Current Rating	20 A tungsten 30 A fluorescent
Number of Poles	8P 8 NO
Control Unit	No control units
Pilot Light	No indicator
Other Options	2P relay (1 NO + 1 NC)
Electrical connection	Screw-clamp terminals
Height	12.68 in (322 mm)
Depth	6.02 in (153 mm)
Width	7.80 in (198 mm)

## Environment

Enclosure Type	NEMA 1 painted sheet steel surface
Product certifications	UL Listed CSA

## Ordering and shipping details

Category	21322 - 8903 LX (NOT L)
Discount Schedule	CP1
GTIN	00785901023388
Nbr. of units in pkg.	1
Package weight(Lbs)	11.68 lb(US) (5.30 kg)
Returnability	No
Country of origin	MX

## Packing Units

Package 1 Height	7.70 in (19.558 cm)
Package 1 width	8.20 in (20.828 cm)
Package 1 Length	13.00 in (33.020 cm)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
PVC free	Yes
Halogen content performance	Halogen free plastic parts product

## Contractual warranty

Warranty	18 months
----------	-----------