



Main

Device short name	IFM
Product or component type	Interface module
Range compatibility	Masterpact MTZ MasterPact NT Masterpact NW ComPact NSX ComPact NS630b...1600 ComPact NS1600b...3200 PowerPact J PowerPact L PowerPact H PowerPact P PowerPact R

Complementary

Communication network type	Universal Logic Plug 2-port RJ45 Modbus, Modbus Serial line slave 9.6...38.4 kbauds 1 RJ45
Mounting mode	By clips
Mounting support	35 mm DIN rail
Accuracy class	Class 2 power supply
Input voltage	24 V DC - 20...10 %
Output voltage	24 V DC
Output current	3 A
Current consumption	30 mA 24 V DC room temperature
Power consumption in W	1.635 W
Memory type	EEPROM data storage
Connections - terminals	RJ45 connector Screw type terminals
Product certifications	EAC CULus CE FCC
Standards	CISPR 22 UL 61010 UL 60950 CISPR 24 CISPR 11 IEC 60950 IACS E10
Height	4.29 in (109 mm)
Width	0.71 in (18 mm)
Depth	2.87 in (73 mm)
Net Weight	4.23 oz (120 g)

Environment

IP degree of protection	Connectors IP20 Other parts: IP30
Relative humidity	5...85 % 131 °F (55 °C) without condensation
Ambient air temperature for storage	-40...185 °F (-40...85 °C)
Ambient air temperature for operation	-4...158 °F (-20...70 °C)
Pollution degree	3
Flame retardance	V0 conforming to UL 94

Shock resistance	+/- 15 gn 11 ms EN/IEC 60068-2-27
Vibration frequency	5...8.4 Hz EN/IEC 60068-2

Ordering and shipping details

Category	01103 - H,J,COMPACT NS UL/IEC CIRCUIT BREAKER ACCESSORIES
Discount Schedule	DE2
GTIN	00785901899280
Nbr. of units in pkg.	1
Package weight(Lbs)	0.21 lb(US) (0.10 kg)
Returnability	Yes
Country of origin	ID

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	1.77 in (4.5 cm)
Package 1 width	3.15 in (8 cm)
Package 1 Length	4.53 in (11.5 cm)
Unit Type of Package 2	S03
Number of Units in Package 2	54
Package 2 Weight	14.69 lb(US) (6.662 kg)
Package 2 Height	11.81 in (30 cm)
Package 2 width	11.81 in (30 cm)
Package 2 Length	15.75 in (40 cm)
Unit Type of Package 3	P12
Number of Units in Package 3	432
Package 3 Weight	163.80 lb(US) (74.3 kg)
Package 3 Height	31.50 in (80 cm)
Package 3 width	31.50 in (80 cm)
Package 3 Length	47.24 in (120 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: Cancer and Reproductive Harm - www.P65Warnings.ca.gov
EU RoHS Directive	Compliant  EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration
Environmental Disclosure	 Product Environmental Profile
Circularity Profile	 End Of Life Information
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------