

# MPR64200

MP Meter Pak, meter center, four ringless sockets, no bypass, 5th jaw, OH, UG, 600 A bus, 200 A, 240 VAC single phase 3W



## Main

Product	Meter Center
Socket Rating	200 A
Main Type	Main Lugs
Number of Jaws	5
Number of Meter Sockets	4
Socket Type	Ringless

## Complementary

Main Rating	600 A 400 A
Bus Rating	600 A
Certifications	UL Listed
Type	Meter-Pak
Busbar Material	Aluminium busbar
Bypass Type	No bypass
Enclosure Material	Steel
Enclosure Rating	NEMA 3R
Maximum Voltage Rating	240 V AC
Mounting	Surface
Phase	1 phase
Service Feed Location	OH UG
Wire Size	AWG 1/0...600 kcmil 1 aluminium AWG 1/0...600 kcmil 1 copper
Wire Configuration	3-wire
Height	52.00 in (1320.80 mm)
Width	29.44 in (747.78 mm)
Depth	8.28 in (210.31 mm)

## Ordering and shipping details

Category	00021 - METER-PAK
Discount Schedule	DE4
GTIN	00785901410478
Nbr. of units in pkg.	1
Package weight(Lbs)	115 lb(US) (52.16 kg)
Returnability	Yes
Country of origin	MX

## Packing Units

Package 1 Height	0.82 ft (0.249 m)
Package 1 width	2.48 ft (0.757 m)
Package 1 Length	4.43 ft (1.351 m)

## Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to <a href="http://www.P65Warnings.ca.gov">www.P65Warnings.ca.gov</a>
REACH Regulation	<a href="#">REACH Declaration</a>
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
China RoHS Regulation	<a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------