

HOM2150BB

Mini branch circuit breaker, Homeline, 150A, 4 pole, 120/240 VAC, 10 kA AIR, standard type, plug in mount



Main

Product	Miniature circuit-breaker
Range	Homeline
Current Rating	150 A
Certifications	UL Listed
Voltage Rating	120/240 V AC
Mounting Type	Plug-in
Number of Poles	4P
Short Circuit Current Rating	10 kA
Number of Spaces	4
Circuit Breaker Type	Standard
Ratings	HACR rated
Electrical Connection	Box lugs
Wire Size	AWG 4...300 kcmil aluminium/copper)1

Complementary

Tightening torque	250.48 lbf.in (28.3 N.m) 0.15...0.23 in ² (95...150 mm ²) (AWG 4/0...250 kcmil)
Height	5.39 in (136.91 mm)
Width	3.98 in (101.09 mm)
Depth	3.13 in (79.50 mm)

Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------

Ordering and shipping details

Category	00144 - HOM BREAKERS 150-200A
Discount Schedule	DE3D
GTIN	00785901296201
Nbr. of units in pkg.	1
Package weight(Lbs)	3.07 lb(US) (1.39 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Package 1 Height	5.80 in (14.732 cm)
Package 1 width	7.00 in (17.780 cm)
Package 1 Length	8.00 in (20.320 cm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	Lifetime
----------	----------

Approximate Dimensions

