



Main

Product or component type	All-In-One
Range of product	Homeline
Meter socket type	Ringed
Hub type	A
Included Options	Circuit breaker 1) 2P 100 A 120/240 V AC main supply ready assembled Circuit breaker 3) 1P 20 A 120 V AC Tandem circuit breaker 3) 1P 20 A 120 V AC

Complementary

Line Rated Current	100 A
Short-circuit current	10 kA
Mounting	Surface
Number of spaces	10
Number of circuits	20
Number of Tandem Breakers	10
Electrical connection	Lugs line side Lugs service ground
Wire Size	AWG 6...AWG 1 aluminium/copper)line side AWG 8...AWG 4 aluminium/copper)service ground
Disconnect	Service disconnect (factory installed)
Disconnect Rating	100 A
Branch Breaker Rating	80 A
Service feed location	OH
Bypass type	No bypass
Width	18.76 in (476.50 mm)
Depth	5.41 in (137.41 mm)
Height	41.18 in (1045.97 mm)

Ordering and shipping details

Category	00148 - HOMELINE CSED DEVICES
Discount Schedule	DE3A
GTIN	00785901396420
Nbr. of units in pkg.	1
Package weight(Lbs)	23.18 lb(US) (10.51 kg)
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	5.50 in (13.97 cm)
Package 1 width	13.70 in (34.798 cm)
Package 1 Length	21.80 in (55.372 cm)
Unit Type of Package 2	PAL
Number of Units in Package 2	35

Package 2 Weight	850.00 lb(US) (385.553 kg)
Package 2 Height	42.00 in (106.68 cm)
Package 2 width	40.00 in (101.6 cm)
Package 2 Length	48.00 in (121.92 cm)

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration

Contractual warranty

Warranty	18 months
----------	-----------