



### Main

Product	Circuit breaker
Range of product	Powerlink
Circuit Breaker Type	ECB-G3
Circuit breaker application	Switching Duty rated HID rated HACR rated
Options	Motor for circuit-breaker 24 V DC
Trip unit technology	Thermal-magnetic, standard, LI

### Complementary

Line Rated Current	30 A
Product certifications	UL Listed CSA
Voltage Rating	480Y/277 V AC
Mounting mode	Bolt-on
Number of Poles	3P
Interrupt Rating	14 KA 480Y/277 V AC 42 kA 240 V AC
Number of spaces required	3
Electrical connection	Bolted connection
Wire Gauge	AWG 12...AWG 8 aluminium AWG 10...AWG 8 copper

### Environment

Ambient air temperature for operation	104 °F (40 °C)
---------------------------------------	----------------




### Ordering and shipping details

Category	09663 - POWERLINK GEN-3 ECB BREAKERS
Discount Schedule	DE8A
GTIN	00785901300175
Nbr. of units in pkg.	1
Package weight(Lbs)	3.79 lb(US) (1.72 kg)
Returnability	Yes
Country of origin	MX

### Packing Units

Package 1 Height	4.40 in (11.176 cm)
Package 1 width	6.70 in (17.018 cm)
Package 1 Length	10.10 in (25.654 cm)

## Offer Sustainability

EU RoHS Directive	Compliant  <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	 <a href="#">Yes</a>
China RoHS Regulation	 <a href="#">China RoHS Declaration</a>

## Contractual warranty

Warranty	18 months
----------	-----------