



Main

Range	TeSys
Device short name	LAD4
Product or component type	Suppressor module
Product compatibility	3P LC1D40A...D80A 4P LC1DT60A...DT80A

Complementary

Mounting location	Front
Mounting mode	By clips
Suppressor technology	Varistor (peak limiting)
[Uc] control circuit voltage	50...127 V DC 50...127 V AC 50/60 Hz
Maximum peak voltage	2 Uc
Net Weight	0.04 lb(US) (0.02 kg)

Environment

Ambient air temperature for operation	-13...131 °F (-25...55 °C)
Ambient air temperature for storage	-40...176 °F (-40...80 °C)

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901661795
Nbr. of units in pkg.	1
Package weight(Lbs)	0.03 lb(US) (0.01 kg)
Returnability	Yes
Country of origin	CZ

Packing Units

Unit Type of Package 1	PCE
Package 1 Height	0.79 in (2 cm)
Package 1 width	1.18 in (3 cm)
Package 1 Length	2.76 in (7 cm)
Unit Type of Package 2	BB1
Number of Units in Package 2	10
Package 2 Weight	6.77 oz (192 g)
Package 2 Height	2.44 in (6.2 cm)
Package 2 width	2.95 in (7.5 cm)
Package 2 Length	4.72 in (12 cm)
Unit Type of Package 3	S01

Number of Units in Package 3	100
Package 3 Weight	4.73 lb(US) (2.145 kg)
Package 3 Height	5.91 in (15 cm)
Package 3 width	5.91 in (15 cm)
Package 3 Length	15.75 in (40 cm)

Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.

Contractual warranty

Warranty	18 months
----------	-----------